

USB 2.0 to Gigabit Ethernet NIC Network Adapter, 10/100/1000 Mbps, White

MODEL NUMBER: U236-000-GBW



Create a Gigabit network port on a computer via USB

Description

Tripp Lite's U236-000-GBW, USB 2.0 Gigabit Ethernet Adapter, allows your computer to instantly connect to a Gigabit network through a USB port - no need to open up your computer case to add an internal Ethernet card. The adapter's compliance with USB 2.0 (480Mbps) ensures true Gigabit network speed without any compromise. Furthermore, the adapter is compact and is USB bus-powered; requires no external power adapter.

Features

- Allows your computer to instantly connect to a Gigabit network through a USB port - no need to open up your computer case to add an internal Ethernet card
- Compliant with USB 2.0 and USB 1.1 specifications
- Compliant with IEEE 802.3 (10Base-T) and 802.3u (100Base-TX) standards
- Supports both full-duplex and half-duplex operations
- Supports suspend mode and remote wakeup via link-up and magic packet
- Powered by USB port - no external power adapter required
- Equipped with diagnostic LEDs
- Windows XP, Vista, 7, 8, and 8.1 compatible
- Mac OSX 10.6 through 10.10 compatible
- Linux Kernel 2.6.25 and later compatible

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332183279 |

Highlights

- Windows, Mac, and Linux compatible
- Compliant with USB 2.0 and USB 1.1 specifications

System Requirements

- IBM compatible Pentium-233MHz or faster PC or Mac
- 64 MB RAM or more
- One available USB port
- Windows XP, Vista, 7, 8, and 8.1 compatible
- Mac OSX 10.6 through 10.10 compatible
- Linux Kernel 2.6.14 and later compatible

Package Includes

- USB Ethernet Adapter
- Quick Start Guide
- Driver CD



| | |
|--------------------------------------|------------------------------------------|
| Technology | Cat5/5e; Cat6; USB 2.0 (High Speed); USB |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 7.5 |
| PHYSICAL | |
| Color | White |
| Cable Jacket Rating | VW-1 |
| Material of Construction | ABS, PVC |
| Shipping Dimensions (hwd / in.) | 0.90 x 5.20 x 5.20 |
| Shipping Weight (lbs.) | 0.14 |
| Unit Dimensions (hwd / in.) | 0.6 x 2.6 x 0.9 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.02 |
| Unit Weight (lbs.) | 0.05 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 158 F (0 to 70 C) |
| Storage Temperature Range | 14 to 176 F (-10 to 80 C) |
| Relative Humidity | 10% to 90 % RH, Non-Condensing |
| BTUs | 3.2 BTU/Hr |
| Power Consumption (Watts) | 0.95 |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps |
| IEEE Standards Supported | 802.3; 802.3ab; 802.3az; 802.3u; 802.3x |
| CONNECTIONS | |
| Side A - Connector 1 | USB A (MALE) |
| Side B - Connector 1 | RJ45 (FEMALE) |
| Connector Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 2.0 (up to 480 Mbps) |
| Driver Required | Yes |
| Recommended Category Cable | Cat5/5e/6 Cables |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|--------------------------------|
| Auto MDIX Support | Yes |
| Full Duplex Support | Yes |
| Suspend Mode Support | Yes |
| Remote Wakeup Support | Yes |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>