

## Keyspan Mini DisplayPort 1.2 to Active VGA Adapter, Video Converter for Mac/PC, Thunderbolt 1 & 2 Compatible, 1920x1200 1080p (M/F)

MODEL NUMBER: P137-000-VGA



Connect a VGA monitor to a Mac or PC with a Mini Displayport output

### Description

Tripp Lite's P137-000-VGA Mini-DisplayPort 1.2 to VGA Adapter allows you to connect a Mac or PC with a Mini-DisplayPort or Thunderbolt™ TM output to a VGA monitor. Ideal for Thunderbolt™ /Mini DisplayPort equipped laptops, Chromebooks, MacBooks, and Microsoft Surface. Mac (up to OSX 10.12) and Windows (up to 10) Compatible.

Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully-molded compact one piece design ensures long life enjoyment.

Features a simple plug and play design with an integrated chip that converts the digital Mini-DisplayPort signal to analog VGA; no drivers or setup needed. Simply plug the adapter into your Mini-DisplayPort /Thunderbolt™ TM source and connect your VGA cable between it and your monitor.

Unlike passive adapters, Active adapters convert both Single-Mode and Dual Mode (DP++) DisplayPort output. Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals.

### Features

- Compact 1-piece design
- Connect a VGA monitor to a Mac or PC/Windows with a Mini DisplayPort or Thunderbolt 1/2 output
- Displayport 1.2 compliant
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p

### Highlights

- Compact 1-piece design
- Connect a VGA monitor to a Mac or PC/Windows with a Mini DisplayPort or Thunderbolt 1/2 output
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

### System Requirements

- Mac (up to OSX 10.12) or PC/Windows (up to 10) with a Mini Displayport port; Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Monitor with a VGA port

### Package Includes

- Mini-Displayport 1.2 to Active VGA Adapter



- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

## Specifications

| OVERVIEW                            |                         |
|-------------------------------------|-------------------------|
| UPC Code                            | 037332184825            |
| Technology                          | VGA/SVGA; DisplayPort   |
| PHYSICAL                            |                         |
| Color                               | Black                   |
| Shipping Dimensions (hwd / cm)      | 4.57 x 9.14 x 13.72     |
| Shipping Dimensions (hwd / in.)     | 1.80 x 3.60 x 5.40      |
| Shipping Weight (kg)                | 0.09                    |
| Shipping Weight (lbs.)              | 0.20                    |
| CONNECTIONS                         |                         |
| Side A - Connector 1                | MINI DISPLAYPORT (MALE) |
| Side B - Connector 1                | HD15 (FEMALE)           |
| STANDARDS & COMPLIANCE              |                         |
| Certifications                      | RoHS                    |
| WARRANTY                            |                         |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>