



B32562

MKT

General purpose (stacked) SilverCap™

15

Ordering codes and packing units (lead spacing 15 mm)

V_R	V_{rms} f ≤ 60 Hz	C_R	Max. dimensions w × h × l	Ordering code (composition see below)	Ammo pack	Reel	Untaped
VDC	VAC	μF	mm		pcs./unit	pcs./unit	pcs./unit
100	63	2.2	4.9 × 8.0 × 16.5	B32562J1225+***	1190	1300	800
		3.3	6.0 × 9.3 × 16.5	B32562J1335+***	960	1000	500
		4.7	7.3 × 10.6 × 16.5	B32562H1475+***	790	900	400
		6.8	9.0 × 11.8 × 16.5	B32562H1685+***	640	700	290
		10	11.8 × 13.0 × 16.5	B32562H1106+000	—	—	200
250	160	0.47	5.0 × 6.7 × 16.5	B32562J3474+***	1190	1300	950
		0.68	6.0 × 7.8 × 16.5	B32562J3684+***	960	1000	500
		1.0	7.0 × 9.3 × 16.5	B32562J3105+***	830	900	500
		1.5	8.7 × 11.0 × 16.5	B32562H3155+***	660	700	300
		2.2	10.7 × 12.8 × 16.5	B32562H3225+000	—	—	200
		3.3	13.9 × 14.5 × 16.5	B32562H3335+000	—	—	150
400	200	0.22	4.7 × 7.5 × 16.5	B32562J6224+***	1240	1300	850
		0.33	6.0 × 8.3 × 16.5	B32562J6334+***	960	1000	500
		0.47	7.3 × 9.3 × 16.5	B32562J6474+***	790	900	450
		0.68	8.9 × 10.8 × 16.5	B32562H6684+***	640	700	300
		1.0	10.9 × 12.5 × 16.5	B32562H6105+000	—	—	200
		1.5	13.7 × 15.2 × 16.5	B32562H6155+000	—	—	100
630	350	0.22	9.2 × 12.2 × 16.5	B32562H8224+000	—	—	350
		0.33	11.2 × 14.2 × 16.5	B32562H8334+000	—	—	250
		0.47	13.5 × 16.3 × 16.5	B32562H8474+000	—	—	180

Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", Section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

J = ±5%

*** = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (lead length 5 – 1 mm)