

Справочник по полупроводниковым диодам -4

Диод	Uоб/Уимп В/В	Iпр/ Iимп А/А	Uпр/ Iпр В/А	Сд/Уд пф/В (Т нс)	Iо (25) / Iом мА/мА	Fmax кГц	P/Pт Вт/Вт
2Д251А	/50	10/150	1.0/10	(50)	0.05/2.0	200	
2Д251Б	/70	10/150	1.0/10	(50)	0.05/2.0	200	
2Д251В	/100	10/150	1.0/10	(50)	0.05/2.0	200	
2Д251Г	/50	10/150	1.0/10	(100)	0.05/2.0	200	
2Д251Д	/70	10/150	1.0/10	(100)	0.05/2.0	200	
2Д251Е	/100	10/150	1.0/10	(100)	0.05/2.0	200	
2Д252А	/80	30/60	0.95/30		2/25		
2Д252Б	/100	30/60	0.95/30		2/25		
2Д252В	/120	30/60	0.95/30		2/25		
2Д253А	800/850	3/9.6	1.5/3	(220)	0.02/1	100	7
2Д253Б	800/850	1/3.2	1.5/1	(220)	0.02/1	100	2.5
2Д253В	600/650	3/9.6	1.5/3	(220)	0.02/1	100	7
2Д253Г	600/650	1/3.2	1.5/1	(220)	0.02/1	100	7
2Д253Д	400/450	3/9.6	1.5/3	(220)	0.02/1	100	2.5
2Д253Е	400/450	1/3.2	1.5/1	(220)	0.02/1	100	2.5
2Д254А	1000/1000	1/3.2	1.5/1	(200)		150	
2Д254Б	800/800	1/3.2	1.5/1	(200)		150	
2Д254В	600/600	1/3.2	1.5/1	(200)		150	
2Д254Г	400/400	1/3.2	1.5/1	(200)		150	
2Д255А5	/60	3/6	0.9/3		2/30	1000	
2Д255Б5	/80	3/6	0.9/3		2/30	1000	
2Д255В5	/100	3/6	0.9/3		2/30	1000	
КД257А	200/200	3/15	1.5/5	(250)	/0.15		
КД257Б	400/400	3/	1.5/5	(250)	/0.15		
КД257В	600/600	3/	1.5/5	(300)	/0.15		
КД257Г	800/800	3/	1.5/5	(300)	/0.15		
КД257Д	1000/1000	3/	1.5/5	(300)	/0.15		
КД258А	200/200	1.5/7.5	1.6/3	(250)	/0.15		
КД258Б	400/400	1.5/	1.6/3	(250)	/0.15		
КД258В	600/600	1.5/	1.6/3	(300)	/0.15		
КД258Г	800/800	1.5/	1.6/3	(300)	/0.15		
КД258Д	1000/1000	1.5/	1.6/3	(300)	/0.15		
КД259А	90/90	3/10	0.8/3				
КД259Б	80/80	3/10	0.8/3				
КД259В	60/60	3/10	0.8/3				
2Д260А5	/40	30/	0.75/30		10/25	500	
2Д260Б5	/60	30/	0.75/30		10/25	500	
КД275А	50/	2.2/	1.4/				0.8/
КД275Б	100/	2.2/	1.4/				0.8/
КД275В	200/	2.2/	1.4/				0.8/
КД275Г	400/	2.2/	1.4/				0.8/
КД275Д	600/	2.2/	1.4/				0.8/
КД275Е	800/	2.2/	1.4/				0.8/
КД282А	/100	5/50	1.0/2			2	
2Д2990А	600/650	20/100	1.4/20	(150)	11/	200	/25
2Д2990Б	400/450	20/100	1.0/20	(150)	11/	100	/25
2Д2990В	200/250	20/100	1.4/20	(150)	11/	200	/25
КД2991А	/45	60/800	0.7/60		/50	200	
2Д2992А	200/250	30/60	1.0/30	(100)	0.2/25	100	3
2Д2992Б	100/200	30/60	1.0/30	(100)	0.2/25	100	3

2Д2992В	50/100	30/60	1.0/30	(100)	0.2/25	100	3
2Д2993А	200/250	20/60	1.0/20	(100)	0.2/25	100	3
2Д2993Б	100/200	20/60	1.0/20	(100)	0.2/25	100	3
2Д2993В	50/100	20/60	1.0/20	(100)	0.2/25	100	3
КД2994А	100/100	20/80	1.4/20	(35)	0.1/2	200	
2Д2995А	50/	20/	1.1/20	(50)	0.01/2	200	
2Д2995Б	70/	20/	1.1/20	(50)	0.01/2	200	
2Д2995В	100/	20/	1.1/20	(50)	0.01/2	200	
2Д2995Г	/150	20/	1.1/20	(50)	0.01/2	200	
2Д2995Д	/200	20/	1.1/20	(50)	0.01/2	200	
2Д2995Е	/100	20/	1.1/20	(100)	0.01/2	200	
2Д2995Ж	/150	25/	1.1/20	(100)	0.01/2	200	
2Д2995И	/200	25/	1.1/20	(100)	0.01/2	200	
2Д2997А	200/250	30/100	1/30	(200)	0.2/25		/30
2Д2997Б	100/200	30/100	1/30	(200)	0.2/25		/30
2Д2997В	50/100	30/100	1/30	(200)	0.2/25		/30
КД2998А	/15	30/	0.6/30		20/100	200	
КД2998Б	/20	30/	0.6/30		20/100	200	
КД2998В	/25	30/	0.7/30		20/100	200	
КД2998Г	/35	30/450	0.7/30		20/100	200	
КД2998Д	/30	30/300	0.7/30		20/100	200	
2Д2999А	200/250	20/100	1/20	(200)	0.2/25		/20
2Д2999Б	100/200	20/100	1/20	(200)	0.2/25		/20
2Д2999В	50/100	20/100	1/20	(200)	0.2/25		/20