

MINI MICRO SWITCH 微動開關

SPECIFICATIONS:

- Contact resistance: 25m Ω maximum (Initial)
- Insulation resistance: 100M Ω minimum (At 500VDC)
- Dielectric strength: 1,000VAC 50/60Hz for 1 minute.
- Contact configuration



ITEM NO.	AZ8122	AZ8112	AZ8111	AZ8200	AZ8169	AZ8166	AZ8108	AZ8107	AZ8104
Operation Force	900g max.	900g max.	900g max.	90g max.	90g max.	90g max.	800g-342g	800g-230g	600g max.
Release Force	150g min.	150g min.	150g min.	150g min.	150g min.	150g min.	50-21g	50-12g	50g min.
Pretravel	1.5mm max.	1.5mm max.	1.5mm max.	30mm max.	30mm max.	30mm max.	20° max.	20° max.	20° max.
Movement Differential	0.7mm max.	0.7mm max.	0.7mm max.	20mm max.	20mm max.	20mm max.	10° max.	10° max.	10° max.
Overtravel	4mm min.	4mm min.	4mm min.	4mm min.	4mm min.	4mm min.	75° min.	75° min.	75° min.
Operating Position	5.5mm min.	5.5mm min.	5.5mm min.	50mm min.	50mm min.	50mm min.	95° min.	95° min.	95° min.