


RoHS
STANDARD
Drawing For Reference Only



Technical requirement :

- 1 . This product should meet EU RoHS related requirement.
- 2 . The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
- 3 . The surface of metal part should be without any defect such as scaur,nick,oxidation and plating problem.
- 4 . The electronic performance should be the same as spec.
- 5 . The un-specified tolerance is : $<6 \pm 0.1$
 $6 \sim 20 \pm 0.2$
 $>20 \pm 0.3$

Specification :

Contact Resistance : 30m ohm max.
 Insulation Resistance : 100M ohm min. at DC 500V
 Dielectric Strength : AC 500V for one minute.

DCI DRAGON CITY INDUSTRIES LIMITED

PART NAME			2.5mm MONO PLUG		TOLERANCE : \pm		DESIGN	K.W LAW	REMARK		SCALE	
PART NO.			NP-101-EN		UNIT: MM		DRAWING	W.K YEUNG	REMARK		MATERIAL	
							CHECK	K.L WONG	REMARK		DWG. NO.	80118-1400
							APPROVAL	K.W CHAN	REMARK		SHEET	