

Crimping pliers - CRIMPFOX-RC 10 - 1212061

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for non-insulated cable lugs, 4 - 10 mm², double indent crimp

Why buy this product

- ✓ The CRIMPFOX-RC 10 completes the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- ✓ All pliers of this type reduce the amount of force required during crimping by 25%



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 453936
Weight per Piece (excluding packing)	660.2 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	Indent crimp
Type of contact	Non-insulated cable lugs
Designation	Crimping position 1
Max. cross section	4 mm ²
AWG max	12
Designation	Crimping position 2
Max. cross section	6 mm ²

Crimping pliers - CRIMPFOX-RC 10 - 1212061

Technical data

General

AWG max	10
Designation	Crimping position 3
Max. cross section	10 mm ²
AWG max	8
Die station	Crimping position 4
	Crimping position 5

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Crimping pliers - CRIMPFOX-RC 10 - 1212061

Approvals

Approvals submitted

Approval details

EAC

Accessories

Accessories

Die

Replacement die - CRIMPFOX-RC 10/DIE - 1212062



Spare die for CRIMPFOX-RC 10

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring
