


## Polyurethane recoils with rigid and swiveling male fittings



### Technical characteristics

**Max operating pressure:** 8 bar

**Temperature:** -15°C to +70°C

**Construction:** Polyurethane

**Highlight:** Non scratch

**Equipped with:** Teflon-coated coupler

Blue

BSPT male thread	ID/OD (mm)	Coil Ø (mm)	Max length (m)	Min. length (m)	Parts Numbers
R 1/4	5 x 8	42	2	0.18	<b>PUS 52</b>
R 1/4	5 x 8	42	4	0.4	<b>PUS 54</b>
R 1/4	5 x 8	42	6	0.6	<b>PUS 56</b>
R 1/4	5 x 8	42	8	0.80	<b>PUS 58</b>
R 1/4	6.5 x 10	52	4	0.4	<b>PUS 64</b>
R 1/4	6.5 x 10	52	6	0.55	<b>PUS 66</b>
R 1/4	6.5 x 10	52	8	0.8	<b>PUS 68</b>
R 1/4	6.5 x 10	52	10	0.95	<b>PUS 610</b>
R 3/8	8 x 12	65	4	0.4	<b>PUS 84</b>
R 3/8	8 x 12	65	6	0.65	<b>PUS 86</b>
R 3/8	8 x 12	65	8	0.72	<b>PUS 88</b>
R 3/8	8 x 12	65	15	1.35	<b>PUS 815</b>