Turn Counting Dial

Model 2600 Series



Features:

- 7/8" diameter
- Analog



| MODEL | | 2606 | 2607 | 2601 |
|------------------------------------|-----------------------------|--------------------------------|------|-----------------|
| Counting Capacity, Maximum Turns | | 20 | | 15 |
| For Shaft Diameter | | 1/4" | | 1/8" |
| For Bushing Diameter | | 3/8" | | 1/4" |
| Depth: Maximum, From Face of Panel | | 0.900" | | 0.82" |
| Shaft Extension: | Maximum, From Face of Panel | 0.781 | | 0.672" |
| | Minimum, From Face of Panel | 0.628 | 3" | 0.469" |
| Bushing Extension: | Maximum, From Face of Panel | 0.300" | | 0.270" |
| Locking Mechanism | | Positive Action with Detent | | Positive Action |
| Weight, Nominal | | 0.60 oz. | | |
| Number of Set Screws | | 1 | 2 | 1 |
| Numeral Height | | 0.050" | | |
| Knob Material | | Black Plastic | | |
| Dial Finish | | Black Numerals on Satin Chrome | | |
| Housing Finish | | Satin Chrome | | |
| Operating Temperature Range | | −55°C to +71°C | | |

| 2606S | 26075 | |
|--------------------------------|--|--|
| 15 | | |
| 1/4" | | |
| 3/8" | | |
| 0.94" | | |
| 0.781" | | |
| 0.57 | 8" | |
| 0.300" | | |
| Positive Action | | |
| 0.60 oz. | | |
| 1 | 2 | |
| 0.050" | | |
| Black Plastic | | |
| Black Numerals on Satin Chrome | | |
| Satin Chrome | | |
| −55°C to +71°C | | |
| | 15 1/4 3/8 0.94 0.78 0.57 0.30 Positive 0.60 1 0.05 Black P Black Numerals on Satin Ch | |

Turn Counting Dial

Model 2600 Series



