



HTSB-2

HEXAGONAL THREADED SPACER,
BRASS

Part No.	Thread "D1" + "D2"		"L" mm	"H" mm	"P1" mm	"P2" mm
HTSB-M2-L-4-2	M2	M2	5.0	4.0	6.0	3.0
			8.0			4.0
			10.0 / 12.0 / 15.0 / 18.0 / 20.0 / 25.0 / 30.0			6.0
HTSB-M2.5-L-5-2	M2.5	M2.5	5.0	5.0	6.0	3.0
			8.0			4.0
			10.0 / 12.0 / 15.0 / 18.0 / 20.0 / 25.0 / 30.0			6.0
HTSB-M3-L-5-2	M3	M3	5.0	5.0	8.0	3.0
			8.0			4.0
			10.0			6.0
			12.0 / 15.0 / 18.0 / 20.0			8.0
			25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0			10.0
HTSB-M3-L-5.5-2	M3	M3	5.0	5.5	8.0	3.0
			8.0			4.0
			10.0			6.0
			12.0 / 15.0 / 18.0 / 20.0			8.0
			25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0			10.0
HTSB-M4-L-7-2	M4	M4	8.0	7.0	8.0	4.0
			10.0			6.0
			12.0 / 15.0 / 18.0 / 20.0			8.0
			25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0			10.0
HTSB-M5-L-8-2	M5	M5	10.0	8.0	8.0	6.0
			12.0 / 15.0 / 18.0 / 20.0			8.0
			25.0 / 30.0 / 35.0 / 40.0 / 50.0 / 60.0			10.0

Material: Brass CuZn39Pb3
 Plating: G3 E nickel to DIN 267
 Max. Torque: 430 N / mm²
 Tolerance: ± 0,1 mm
 Std. Pk.: 100 pcs.

Note:
 HTSB M3 L 5.5 2
 Part Thread Length SW Type