


**Product family:** Brass cable glands - Gas thread  
**Item code:** 2450, 2451, 2452, 2453, 2454, 2455, 2456, 2457, 2458, 2459, 24592, 24593  
**Description:** BRASS CABLE GLANDS · GAS THREAD · IP54 · STANDARD

**Image**




**Technical drawing**



**Specifications**

**MATERIAL:** nickel-plated brass  
**OPERATING TEMPERATURE:** from -20 °C to +70 °C  
**INNER GASKET:** NBR (nitrile rubber), 70 Shore A  
**ASSEMBLY:** tighten on a flat and smooth surface

Code	Gas thread (ISO228/1) (°)	Ø cable (mm)	L (mm)	E wrench (nut)	E1 wrench (locknut)	
2450	G 1/4"	4 - 6	5	14	13	100/100
2451	G 3/8"	8 - 10	6	17	15	100/100
2452	G 1/2"	10 - 12	7	22	20	100/100
2453	G 5/8"	12 - 14	7,5	24	22	100/100
2454	G 3/4"	17 - 19	8,5	30	28	100/100
2455	G 1"	19 - 22	9	35	33	50/50
2456	G 1 1/8"	26 - 28	10,5	40	37	50/50
2457	G 1" 1/4"	26 - 30	10,2	45	42	25/25
2458	G 1" 1/2"	33 - 35	12	50	47	20/20
2459	G 2"	43 - 45	12	64	60	20/20
24592	G 2 1/2"	55 - 57	12	80	80	3/3
24593	G 3"	67 - 69	20	95	95	3/3



**IP54**