
5 CONTACTS WHITE FEMALE HOUSING FOR WIRE INSULATION Ø1.30 TO Ø1.70


UNLESS OTHERWISE SPECIFIED			
.X	±0.38		
.XX	±0.25		
XXX	+0.13		

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER
ORIGINAL 1









NOTE:

ELECTRICAL SPECIFICATIONS:

VOLTAGE RATING: 250V MAX. CURRENT RATING: 3A per CONTACT CONTACT RESISTANCE: $15m\Omega$ MAX. INSULATOR RESISTANCE: $1000M\Omega$ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC(RMS) OPERATING TEMPERATURE: -40 °C ~ 105 °C

MATERIAL & FINISH:

HOUSING: PBT, UL94V-0

CONTACTS: PHOSPHOR BRONZE, TIN PLATED

SEALS: SILICONE RUBBER

L328 IC	THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES
CRET	THE EUROPEAN UNION DIRECTIVES
COMPLIANT	

560 SERIES	WATERPROOF	CONNECTOR



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

	 	
SCALE: 2:1	SHEET 1 OF 1	
CHECKED:	DATE:	
DRAWN: C.B	DATE: July 23, 2020	
ACAD REFERENCE NO.:	560 Assembly	

 DRAWING NUMBER:
 560 Assembly
 ISSUE

 PART NUMBER:
 560-005-000-211
 1