





European P.C.B. type terminal blocks / EK series



EEHK508V



Pitch: 5.08mm

Approval	 	
Technical Data	UL	IEC
Rated voltage	300V	250V
Rated current	25A	24A
Wire range		2.5mm ²
Solid wire (AWG)	24~12	
Stranded wire (AWG/mm ²)	24~12	
Rated surge voltage (UL/IEC/Max.)	1.6 / 1.25 / 4 KV	
Torque (Lb-in)	4	
Screw	M2.5	
Wire strip length	6~7mm	
Pole	Cat. No.	
2x2	EEHK508V-04P	
3x2	EEHK508V-06P	

TEL: +886-2-2908-0614

FAX: +886-2-2908-8549

E-mail: infor@dinkle.com.tw