



---

# SUHNER<sup>®</sup> COAXIAL CONNECTOR DATA SHEET

---

## TYPE 33 BNC-N-Q50-4

---

### Description

Quick mate adaptor  
Quick mate interface : BNC = plug  
Standard interface : N = jack

- test+measurement applications
- pluggable without coupling nut

### General Information

BNC Interface according to: IEC 169-8, MIL-STD-348A/301, CECC 22120  
N Interface according to: IEC 169-16, MIL-STD-348A/304, CECC 22210  
Weight: 38.6 g / 1.36 oz

### Electrical Data

Impedance: 50  $\Omega$   
Frequency range for standard interface: DC ... 11,0 GHz

### Material Data

BNC Centre contact:  
BNC Outer contact:  
BNC Body:  
N Centre contact:  
N Outer contact:  
N Body:  
Insulator:  
Coupling nut:  
Fastening nut:  
Gasket:  
Washer:

### Material

Copper-Beryllium  
Brass  
Brass  
Copper-Beryllium  
Brass  
Brass  
PTFE / PFA  
Brass  
-  
-  
-

### Surface Plating

SUCOPRO  
SUCOPLATE<sup>®</sup>  
SUCOPLATE<sup>®</sup>  
SUCOPRO  
SUCOPLATE<sup>®</sup>  
SUCOPLATE<sup>®</sup>  
  
SUCOPLATE<sup>®</sup>

### Packaging

Single

### Attachments

Outline drawing No.: 32249

### Notes

Order as 33 BNC-N-Q50-4/133 NE under Article No 23003163

---

#### WAIVER!

While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be construed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.



**HUBER+SUHNER**

HUBER+SUHNER AG  
RF Interconnections  
CH-9100 Herisau  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
<http://www.hubersuhner.com>

Issued: 19.8.1999 18:06 Document No.: 23003163A