

# DATA SHEET

## MHD45PK SERIES | METALISED PLASTIC D-SUB HOOD



Size	A	B	C
9 Way	31.0	36.3	15.0
15 Way	39.5	41.3	15.0
25 Way	53.2	40.3	15.0
37 Way	69.7	40.3	15.0

### Main Features

Available in size 9, 15, 25, 37

Suitable for any common D-Sub connector

Strain relief inserts ensure a secure termination

Re-openable

Strain relief inserts ensure a secure termination

Recyclable

Company logo available on request

### Technical Specification

Material	UL Recognised Plastic Material
Operating Temperature	-40°C to 120°C
Cable Entry	Top
Thumb Screws	UNC 4-40 (Standard), M2.5 or M3 on request
Cable Diameter	Up to 13.0mm