


150-250 kg

Industrial Castors Series 3470

Housing made of pressed steel, zinc-chromatised, protected double ball bearing swivel head, dustguard, wheel axle with nut



Wheel: UFR
 Wheel centre: Polyamide, black
 Tread: Elastic-tyre, blue, non-marking, without threadguards, roller bearing




3470 UFR 125 P62

Swivel Castor										
		mm	mm	mm	mm	mm	mm	mm	mm	kg
3470 UFR 100 P62 blue		100	34	105 x 85	80/77 x 60	9	41	128	150	
3470 UFR 125 P62 blue		125	40	105 x 85	80/77 x 60	9	40	155	250	



3478 UFR 125 P62

Fixed Castor										
		mm	mm	mm	mm	mm	mm	mm	mm	kg
3478 UFR 100 P62 blue		100	34	103 x 85	80/77 x 60	9		128	150	
3478 UFR 125 P62 blue		125	40	103 x 85	80/77 x 60	9		155	250	




3477 UFR 125 P62

Swivel Castor with total lock										
		mm	mm	mm	mm	mm	mm	mm	mm	kg
3477 UFR 100 P62 blue		100	34	105 x 85	80/77 x 60	9	41	128	150	
3477 UFR 125 P62 blue		125	40	105 x 85	80/77 x 60	9	40	155	250	


Please indicate required "Elastic-tyre **blue**" when ordering.

Directional locking castors are available in all sizes, see page 180.

Fixing Plates:



Swivel Castor P62-105x85



Fixed Castor P62-103x85