

**A2G-25 0 Pa...1000 Pa same range in m3/s,m3/h,cfm,l/s,  
SCFH,CC/min,LPM,kPa,mbar,mmWC,in.WC**

**A2G-25 air2guide - airflow transmitter**

Item number:	40388217	
Quantity:	1 pcs.	
Order code:	A2G-25-DAZ1-ZM1-SF1-ZZZZ	2Z
Overview:	A2G-25 0 Pa...1000 Pa same range in m3/s,m3/h,cfm,l/s, SCFH,CC/min,LPM,kPa,mbar,mmWC,in.WC A2G-25 air2guide - airflow transmitter Output signal: 4...20 mA, 0...10 V 3-wire Digital display: integrated serial number on dial: Serial number *...*Ingress protection: IP 54 Additional ordering information: without Certificates: without	
Details:	A2G-25 air2guide - airflow transmitter Standard accessories 2 mounting screws Specifications according to data sheet: SP 69.04 Unit: Pa Scale range: 0 Pa...1000 Pa same range in m3/s,m3/h,cfm,l/s, SCFH,CC/min,LPM,kPa,mbar,mmWC,in.WC Digital display: integrated Output signal: 4...20 mA, 0...10 V 3-wire Front panel design: standard air2guide Ingress protection: IP 54 serial number on dial: Serial number *...* Certificates: without Additional ordering information: without	