


**Specification:**

Model	DC.CAB.4400.0020
DC Socket	5.5/2.5 mm
Recommended voltage	0 - 48V
Max Current	5A
Dielectric Strength	500 VDC
Operating temperature	-25°C to +70°C
Cord Length	250 mm
Cable Diameter	Ø 4 mm
Wire Diameter	2x0,5mm ²
ROHS	+

**Made in Poland**