

Products

Micro Speaker

Micro Speaker

Micro Speaker

KDMG26008

PRINT


Shape

KDMG26008




Rated Input(W)	0.2
Maximum Input(W)	0.3
Impedance (?)	8±15%@1.0KHz 1.0V
Rated Frequency (Hz)	520±20%@1.0V
Sound Pressure Level (dB)	92±3dB(0.2W/10cm),79 ±3dB(1W/1m)
Frequency Range (Hz)	Fo--6.5K
Magnet (mm)	∅.5x1.5 Nd-Fe-B
Operating Temperature (?)	-20~+55
Weight (Gram)	5.0
Material	Metal

Dimension



Characteristic / Schematic Diagram



Back

TOP

Part Number Search

Hot Product



High SNR Microphone

∅10*4.5

[More info](#)



Array Microphone

24 x 8 x 2.8

[More info](#)

NEWS

▶ ? [electronica 2010 ?](#)
 Hall B6, Booth
 No.118 **NEW** [..More info](#)

▶ ? [TAITRONICS](#)
 2010? Taipei World
 Trade Center
 Nangang Exhibition
 Hall,Booth
 No.L1019/1021 **NEW**
[..More info](#)

▶ [KINGSTATE Ultra-Thin ESL Speaker and Danish AM3D Audio Software Demo Event Successfully Held On May 12, 2010](#) **NEW** [..More info](#)