

Completely pre-assembled Signal Towers / KOMPAKT 37
K37 cable EM 12VAC/DC GN/RD



Part No.:	698.120.74
Series:	Kompakt 37



MECHANICAL DATA	
Height	141 mm
Diameter	38 mm
Materials	PC
Dome colour	Green Red
Housing colour	Black
Protection category	IP65
Connection	Cable
cross-sectional area maximum	0,34mm ² / 22AWG
Cable entry	Membrane grommet
Cable entry minimum	d = 1 mm
Cable entry maximum	d = 9 mm
Cable length	2000 mm
Tension relief	Pull-out protection
Type of fixing	Built-in mounting
Working temperature minimum	-20°C
Working temperature maximum	+50°C
UL Type Rating	Type 12 Type 4X
Weight with packaging	1 g
Product weight	1 g

ELECTRICAL DATA	
Operating voltage	12V
Operating voltage type	AC/DC
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	12 VDC
Rated operational current	175 mA
Rated inrush current	500 mA
Protection class	Protection class 2
Pollution degree	3 In the connection area: 2


OPTICAL DATA	
Light source	LED
Light colour	Green Red
Optical signal image	Permanent

! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

Completely pre-assembled Signal Towers / KOMPAKT 37
K37 cable EM 12VAC/DC GN/RD

Service life optical	50,000 h maximum
----------------------	------------------

DRAWING



! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.