

## Section Links

A045 | A040 | A095 | A090 | **A195** | A190 | A080 | A085 | A087 | A200 | A070 | A210 | A300 | A315 | A089 | A125 | A105 | A205

## Product Details

**A195** Bolt Down Plastic Base / Stainless Steel Stud

**Materials** Base - Polyamide Reinforced Nylon  
Stud - Stainless Steel type 303



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Bolt Down Centres C1 (mm)	Overall Height H (mm)	Hole Diameter d (mm)	Maximum Recommended Load (kg)
A195/015	M12	75	100	80	117	10	1000
A195/016	M12	125	100	80	167	10	1000
A195/017	M12	150	100	80	192	10	1000
A195/005	M16	75	100	80	120	10	2000
A195/010	M16	125	100	80	170	10	2000
A195/002	M16	150	100	80	195	10	2000
A195/004	M16	200	100	80	245	10	2000
A195/025	M20	125	100	80	174	10	2000
A195/001	M20	150	100	80	199	10	2000
A195/003	M20	200	100	80	249	10	2000
A195/024	M24	125	100	80	178	10	2000
A195/006	M24	150	100	80	203	10	2000
A195/007	M24	200	100	80	253	10	2000
A195/012	M24	250	100	80	303	10	2000

*Dimensions are approximate*

