



**M8 MALE 0° SHIELDED WIREABLE SCREW TERM.**3-pol. 0,14...0.5mm<sup>2</sup>

Male straight

3-pole, shielded

Screw terminals

Connection cross section: 0.14...0.5 mm<sup>2</sup>[Link to Product](#)**Illustration**



Product may differ from Image

### Approvals



### Form

08641

### Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.14...0.5 mm <sup>2</sup>
Sealing range (cable diameter)	3.5...5.5 mm
Protection	IP67 inserted and tightened (EN 60529)

### General data

Temperature range	-25...+85 °C
Dimensions H × W × D	55×14×14 mm

### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1