

ENGLISH

Datasheet

Stock No: 499-2622

RS Pro Stainless Steel Single Check Valve, 1/2 in BSP



Product Details

CF8M Stainless Steel Check Valves

RS Pro Brand Screwed End Swing Check Valves that allow liquids to flow in only one direction.

Features:

1/2 - 3" (DN15 - DN80) W.P: 200 WOG W.T: -20°C - 200°C (-4°F - 392°F) Investment casting

Socket weld (option)

Thread type: ASME B1.20.1 (NPT), DIN 2999 & BS21, ISO7/1 & EN10226

Material:

Body, Cap & Disc - ASTM A351-CF8M Seal & Gasket - PTFE Plug - AISI 316 Bolt - AISI 304

Specifications:

Туре	Single
Connection	1/2 in BSP
Body Material	Stainless Steel
Maximum Working Pressure	14 bar
Thread Size	1/2in
Thread Standard	BSP