

Specification Sheet

Part Number: 110-80001

Tensions and provides clean, flush cuts for 50lb. to 250lb. cable ties, including wide strap ties.

Impact-resistant housing and durable components for extended service life.

Easy-to-adjust tension knob offers 33 different settings for precise, repeatable applications.

Advanced ergonomic design minimizes necessary hand force and “kickback” to reduce repetitive-motion injuries.



EVO 9 Mechanical Hand Tool, Short Hand Span 80 mm, 1/pkg

Article Number 110-80001

Type EVO9SP

Color Red (RD) Black (BK)

Product Description HellermannTyton's EVO 9 manual cable tie application tool combines durability, precision and control with unparalleled comfort. Manufactured with high-performance materials and components, the EVO 9 cuts cable ties with up to 250-lb tensile strength. Its innovative, ergonomic design minimizes the stress on hands and wrists and “kickback” that occur with traditional tools, reducing the risk of repetitive-motion injuries. The HT model offers high tension while the SP model features a smaller grip.

Short Description EVO 9 Mechanical Hand Tool, Short Hand Span 80 mm, 1/pkg

Global Part Name	EVO9SP-MET/PL-BK/RD
Technical Description	Short Hand Span 80mm
Length L (Imperial)	7.5
Length L (Metric)	191
Width W (Imperial)	1.3
Width W (Metric)	33
Cable Ties	T50, T80, T120, T150, T250, T255, WS, LK2, LK3, LK5, GL, ECO Series Ties
Height H (Imperial)	5.3
Height H (Metric)	135
Tension Setting Tools	Adjustable
Cable Tie Width Max (Imperial)	0.5
Material	Metal (MET) Plastic (PL)
Material Shortcut	PL MET
ROHS Compliant	Yes

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8205599000

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)