

## Specification Sheet

Part Number: 151-00644



H-profile of the saddles allows for broad surface contact with the bundle, which minimizes pinching and crushing of the bundle.

Swivels in 360-degree motion to accommodate any area.

Accommodates T50–T250 ties to handle both light-duty and heavy-duty applications.

Dual Swivel Saddle Spacer for T50-T250, Bundle Diameter 0.25 - 3.0", PA66HS/POM, Black, 50/pkg

**Article Number** 151-00644

**Type** DSWS4

**Color** Black (BK)

**Quantity Per** bag

**Product Description** These saddle spacers are installed between two bundles (such as wires, cables, hoses, tubing, conduit, etc.) to separate and prevent chafing and wear. The mounts can be easily rotated by hand, allowing the bundles to be crossed and rotated at any angle. Cable ties, which secure the bundles, are used with the mounts. The dual swivel saddle spacers accommodate cable ties up to 1/2" wide.

**Short Description** Dual Swivel Saddle Spacer for T50-T250, Bundle Diameter 0.25 - 3.0", PA66HS/POM, Black, 50/pkg

**Global Part Name** DSW54-PA66HS/POM-BK

**Length L (Imperial)** 0.91

**Length L (Metric)** 23.6

**Width W (Imperial)** 0.8

**Width W (Metric)** 20.3

**Bundle Diameter Min (Imperial)** 0.3

**Bundle Diameter Min (Metric)** 6.0

**Bundle Diameter Max (Imperial)** 3.0

**Bundle Diameter Max (Metric)** 76.0

**Cable Ties** T50 - T250

**Height H (Imperial)** 0.7

**Height H (Metric)** 18.0

**Cable Tie Width Max (Imperial)** 0.5

**Cable Tie Width Max (Metric)** 12.7

<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS) Polyacetal (POM)
<b>Material Shortcut</b>	POM PA66HS
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C) -31°F to +185°F (-35°C to +85°C)
<b>Minimum Extraction Force (Imperial)</b>	100.0
<b>Minimum Extraction Force (Metric)</b>	445
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	50
<b>Package Quantity (Metric)</b>	50
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00644](#)