

Specification Sheet

Part Number: 151-01528



One base fits more surfaces – flat, curved and moderately angled – for versatile applications.

High-strength, weather-resistant adhesive offers excellent performance indoors and out.

4-way opening allows parallel or perpendicular cable routing options.

Article Number 151-01528

Type FMB4APT-I

Color White (WH)

Quantity Per bag

Product Description

HellermannTyton FlexTack Adhesive Cable Tie Mounts deliver excellent mounting performance on flat, curved and moderately angled surfaces. Use in combination with 18- through 50-pound cable ties to provide stability when securing bundles. Excellent performance in extreme environmental conditions for a wide range of indoor and outdoor applications; on varnished, powder coated, metal or plastic surfaces; in electrical equipment; and where drilling a hole is not possible or desirable. The 4-way saddle allows cable ties to be inserted parallel or perpendicular to the wire bundles.

Short Description	Flexible Cable Tie Mounting Base, 1.1" x 1.1", 0.21" Max Tie Width, PA66HS, White, 100/pkg
Global Part Name	FMB4APT-I-PA66HS-WH
Length L (Imperial)	1.1
Length L (Metric)	28.0
Fixation Method	Self-Adhesive
Width W (Imperial)	1.1
Width W (Metric)	28.0
Cable Ties	T18 - T50
Height H (Imperial)	0.25
Height H (Metric)	6.3
Cable Tie Width Max (Imperial)	0.213
Cable Tie Width Max (Metric)	5.4
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Adhesive	Acrylate with base of acrylic foam
Flammability	UL 94 V-2 (excluding adhesive)
Adhesive Operating Temperature	-31°F to +158°F (-35 °C to +70 °C)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01528](#)