

Specification Sheet

Part Number: 151-01699



Integrated design allows for easy insertion by hand.

1.5–2.0 mm panel thickness range allows for multiple applications.

Double-compression design that accommodates various sizes of wire and cable.

Presents a high extraction force for withstanding extreme conditions.

Low Profile Metal Edge Clip, 1.5 - 2.0mm Panel Thickness, 4.1 - 7mm Cable Range, SS304, 100/bag

Article Number 151-01699

Type MSC2LP

Color Metal (ML)

Quantity Per bag

Product Description Designed for more confined areas, HellermannTyton's Low Profile Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Metal Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. The Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.

Short Description	Low Profile Metal Edge Clip, 1.5 - 2.0mm Panel Thickness, 4.1 - 7mm Cable Range, SS304, 100/bag
Global Part Name	MSC2LP-SS304-ML
Length L (Imperial)	0.67
Length L (Metric)	17.0
Width W (Imperial)	0.375
Width W (Metric)	9.50
Bundle Diameter Min (Imperial)	0.161
Bundle Diameter Min (Metric)	4.1
Bundle Diameter Max (Imperial)	0.276
Bundle Diameter Max (Metric)	7.0
Panel Thickness Min (Imperial)	0.06
Panel Thickness Max (Imperial)	0.078
Panel Thickness Min (Metric)	1.5
Panel Thickness Max (Metric)	2.0

Material	Stainless Steel (SS304)
Material Shortcut	SS304
Flammability	Non-burning
Halogen Free	No
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	7326908695

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01699](#)