

## Specification Sheet

Part Number: CTM410C2



KR/CTM series are designed to provide stability to wire bundles. These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Cable Tie Anchor Mount, .86" x .62", .25" Hole Dia, .31" Max Tie Width, PA66, White, 100/pkg

**Article Number** 151-30703

**Type** CTM4

**Color** White (WH)

**Quantity Per** bag

**Product Description** Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.

**Short Description** Cable Tie Anchor Mount, .86" x .62", .25" Hole Dia, .31" Max Tie Width, PA66, White, 100/pkg

**Global Part Name** CTM4-PA66-WH

<b>Length L (Imperial)</b>	0.86
<b>Length L (Metric)</b>	21.8
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.62
<b>Width W (Metric)</b>	15.8
<b>Cable Ties</b>	T18 - T120
<b>Height H (Imperial)</b>	.37
<b>Height H (Metric)</b>	9.40
<b>Cable Tie Width Max (Imperial)</b>	0.31
<b>Cable Tie Width Max (Metric)</b>	7.9
<b>Mounting Hole Diameter D (Imperial)</b>	0.25
<b>Mounting Hole Diameter D (Metric)</b>	6.4 mm
<b>Mounting Hole Diameter D Max (Metric)</b>	6.4
<b>Material</b>	Polyamide 6.6 (PA66)

<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V-2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL   ANSI/UL 746B UL   ANSI/UL 1565 UL   ANSI/UL 62275
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity (Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTM410C2](#)