

Specification Sheet

Part Number: FC1.2AK2



Adjustable height feature allows the clamp to close to the exact height of the ribbon cable.

Releasable for easy access to cables when necessary.

Flat Ribbon Cable Clamp, Adhesive, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Article Number 154-00013

Type FC1.2A

Color Gray (GY)

Quantity Per bag

Product Description HellermannTyton's flat ribbon clamps route, protect, and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary.

Short Description Flat Ribbon Cable Clamp, Adhesive, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Global Part Name FC1.2A-PA66-GY

Length L (Imperial) 0.81

Length L (Metric) 20.57

Width W (Imperial) 1.5

Width W (Metric) 38.1

Height H (Imperial) 0.5

Height H (Metric) 12.7

Cable Tie Width Max (Imperial) 1.2

Cable Tie Width Max (Metric) 30.48

Mounting Hole Diameter D (Imperial) 0.157

Mounting Hole Diameter D (Metric) 4.0 mm

Mounting Hole Diameter D Min (Imperial) 0.157

Mounting Hole Diameter D Max (Imperial) 0.157

Mounting Hole Diameter D Max (Metric) 4.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Acrylate with base of polyurethane foam
Flammability	UL 94 V-2 (excluding adhesive)
Adhesive Operating Temperature	to +230°F (+110°C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FC1.2AK2](#)