

Specification Sheet

Part Number: TELS-H



Continuous strap and separate heads allow for any bundle diameter, eliminating waste.

Smooth strap prevents cable damage.

UV resistant materials contain an inhibitor which prolongs the life of the tie in outdoor environments.

Extended-Length Tie Heads, POM, Black, 25/pkg

Article Number 111-31000

Type EL-TY (TELSH)

Color Black (BK)

Quantity Per bag

Product Description Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.

Short Description Extended-Length Tie Heads, POM, Black, 25/pkg

Global Part Name	EL-TY (TELSH)-POM-BK
Contents of pkg/kit	25 Heads
Minimum Tensile Strength (Imperial)	250.0
Minimum Tensile Strength (Metric)	1115.0
Length L (Imperial)	0.62
Length L (Metric)	15.75
Fixation Method	2 piece
Identification Plate Position	none
Releasable Closure	No
Tie Closure	steel pawl
Variant	Extended Length
Width W (Imperial)	0.8
Width W (Metric)	20.3
Height H (Imperial)	.49
Height H (Metric)	12.40
Cable Tie Width Max (Metric)	12.7

Material	Polyacetal (POM)
Material Shortcut	POM
Material Cable Tie	Polyacetal (POM)
Material Head	Polyacetal (POM)
Flammability	UL 94 HB
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TELS-H](#)