



COB connector Ø 40 mm for LED array 15.85 x 15.85 mm 47.319.6105.50



0,75 mm²



0,75 mm²

COB connector Ø 40 mm for LED array 15.85 x 15.85 mm 47.319.6105.50



DESCRIPTION

With integrated reflector interface
Screw mounting: for screws M3 and locking washer
Max. torque for screw fixing 0.5 Nm*
Strip length: 7-1 mm
Polarity of LED must be observed
Specifications of LED manufacturer must be observed
cURus: For limited applications
VDE-Reg. No. E289
*Please note the max torque of the COB manufacturer

Product name:	COB connector Ø 40 mm for LED array 15.85 x 15.85 mm
Mounting method 1:	Screw mount
Mounting method 2:	P2F fixing with 28.902.-102
Prefixation of COB:	Yes
Material:	Housing: PBT Contacts: CuSn
LED manufacturer:	Bridgelux, Cree
LED Typ:	CXA/CXB 15xx, H9
Conductor cross-section:	0.5 mm ²
Approval:	cURus
cULus file no.:	E-345385
Rating:	Rating: 3A / 150 VDC
Weight:	5
Pkg.:	420

Suitable for the following LED models:

LED Manufacturer	LED Type	More Information
Bridgelux	H9	http://www.bridgelux.com
Cree	CXA/CXB 15xx	http://www.cree.com