




# Cable assemblies, 1.5 mm<sup>2</sup>

			Extension cable		Connection cable		Connection cable		
			3 x 1.5 mm <sup>2</sup> Female – Male with locking device		3 x 1.5 mm <sup>2</sup> Female – Free end with ultrasonically welded wire ends <sup>3)</sup> Sheath strip length: 35 mm Insulation strip length: 9 mm Cable diameter <sup>2)</sup> : HO5VV: 7.4 – 9.4 mm HO7RNF: 9.2 – 11.9 mm		3 x 1.5 mm <sup>2</sup> Male – Free end with ultrasonically welded wire ends and locking device Sheath strip length: 35 mm Insulation strip length: 9 mm Cable diameter <sup>2)</sup> : HO5VV: 7.4 – 9.4 mm HO7RNF: 9.2 – 11.9 mm		
Cable assemblies									
Cable <sup>1)</sup>	Color	Length <sup>2)</sup>	Part No.	Std. Pack	Part No.	Std. Pack	Part No.	Std. Pack	
HO5VV	gray	1.0 m	96.232.1000.0		96.232.1003.0		96.232.1004.0		
		2.0 m	96.232.2000.0		96.232.2003.0		96.232.2004.0		
		3.0 m	96.232.3000.0		96.232.3003.0		96.232.3004.0		
		4.0 m	96.232.4000.0		96.232.4003.0		96.232.4004.0		
		5.0 m	96.232.5000.0		96.232.5003.0		96.232.5004.0		
		6.0 m	96.232.6000.0		96.232.6003.0		96.232.6004.0		
		7.0 m	96.232.7000.0		96.232.7003.0		96.232.7004.0		
		8.0 m	96.232.8000.0		96.232.8003.0		96.232.8004.0		
	Cable: black	black	1.0 m	96.232.1000.1		96.232.1003.1		96.232.1004.1	
			2.0 m	96.232.2000.1		96.232.2003.1		96.232.2004.1	
			3.0 m	96.232.3000.1		96.232.3003.1		96.232.3004.1	
			4.0 m	96.232.4000.1		96.232.4003.1		96.232.4004.1	
			5.0 m	96.232.5000.1		96.232.5003.1		96.232.5004.1	
			6.0 m	96.232.6000.1		96.232.6003.1		96.232.6004.1	
			7.0 m	96.232.7000.1		96.232.7003.1		96.232.7004.1	
			8.0 m	96.232.8000.1		96.232.8003.1		96.232.8004.1	
HO7RNF	gray	1.0 m	96.232.1030.0		96.232.1033.0		96.232.1034.0		
		2.0 m	96.232.2030.0		96.232.2033.0		96.232.2034.0		
		3.0 m	96.232.3030.0		96.232.3033.0		96.232.3034.0		
		4.0 m	96.232.4030.0		96.232.4033.0		96.232.4034.0		
		5.0 m	96.232.5030.0		96.232.5033.0		96.232.5034.0		
		6.0 m	96.232.6030.0		96.232.6033.0		96.232.6034.0		
		7.0 m	96.232.7030.0		96.232.7033.0		96.232.7034.0		
		8.0 m	96.232.8030.0		96.232.8033.0		96.232.8034.0		
	Cable: black	black	1.0 m	96.232.1030.1		96.232.1033.1		96.232.1034.1	
			2.0 m	96.232.2030.1		96.232.2033.1		96.232.2034.1	
			3.0 m	96.232.3030.1		96.232.3033.1		96.232.3034.1	
			4.0 m	96.232.4030.1		96.232.4033.1		96.232.4034.1	
			5.0 m	96.232.5030.1		96.232.5033.1		96.232.5034.1	
			6.0 m	96.232.6030.1		96.232.6033.1		96.232.6034.1	
			7.0 m	96.232.7030.1		96.232.7033.1		96.232.7034.1	
			8.0 m	96.232.8030.1		96.232.8033.1		96.232.8034.1	

<sup>1)</sup> Other cables available on request  
<sup>2)</sup> Other lengths available on request  
<sup>3)</sup> According to VDE0281, T5 and VDE0288, T4