

FEATURES

- Inductive sensors offer precise detection
- The sensors are completely encapsulate
- IP rating of 67 and are built from a nickel-brass housing
- Additional features include a short circuit
- 2m PVC pre-wired

RS PRO M18 x 1 Inductive Sensor - Barrel, NPN-NO Output, 8 mm Detection, IP67, Cable Terminal

RS Stock No.: 701-8257



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing the range of RS PRO Inductive Proximity Sensors. These versatile and high-quality sensors are an essential addition to any environment where measurement of attributes like pressure, thickness, etc. are integral to business operations, like manufacturing plants and industrial environments. With the RS PRO seal of approval, you are guaranteed a premium performance product, without the premium product price tag.

General Specifications

| | |
|--------------------------------------|--------|
| Sensing/Detection Range | 8mm |
| Output Type | NPN-NO |
| Connection/Terminal Type | Cable |
| Cable length | 48mm |
| Minimum Operating Temperature | -25°C |
| Maximum Operating Temperature | +75°C |

Electrical Specifications

| | |
|--|-----------------|
| Operating Supply Voltage | 10V→30Vdc |
| Switching Current | 200 mA |
| Switching Frequency | 1kHz |
| Voltage drop | ≤2V |
| Temperature drift / Hysteresis | ±10% / 5%...15% |
| Wiring technique | 3 wire |
| Contact maximum DC Voltage | 30V |
| Short Circuit Overload Protection | YES |
| Reverse Polarity Protection | YES |
| Overload Protection | YES |

Mechanical Specifications

| | |
|---------------------------------------|-----------------------------|
| Body Style | Barrel |
| Mounting Type | Non Flush |
| Thread Size | M18 x 1 |
| Housing Material | Nickel Plated Brass |
| Length | 48mm |
| Shock and Vibration Resistance | 30g, 11 ms/10Hz ...55Hz,1mm |

Protection Category

| | |
|------------------|------|
| IP Rating | IP67 |
|------------------|------|

Approvals


| | |
|----------------------------------|--|
| Compliance/Certifications | cULus Listed, EN 60947-5-2, RoHS Compliant, UL |
|----------------------------------|--|



Inductive Proximity Sensors

Dimensional drawing (Dimensions in mm (inch))


IME18 Short-body housing, cable, non-flush



1. Connection
2. Indication LED
3. Fastening nuts (2x); width across 24, metal

Installation

Non-flush installation



Connection diagram

Cd-001

