

## **TECHNICAL DATA SHEET**

Part#: 9231E

Cutters - Small Oval Head -★★★★- Carbon Steel

The 9231E five star Lazer Line® small oval maximum flush cutter has a cutting capacity of .040" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the Lazerlok™ joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

Precision Level

Material

Surface Resistivity

Shape

Type of Cut

• Group

 Cutting Capacity Blade Angle

• Blade Length

• Body Width

Body Height

OAL

• Weight (OZ)

UPC

Schedule B

• ECCN

• UNSPSC Code

Country of Origin

\*\*\*\*

Carbon

10<sup>10</sup> ohms/sq

Round Head

Optimum Flush

**Cutting Tools** 

32 - 18 AWG / .008 - .040" / .2 - 1 mm

14.25°

.24" (6mm)

0.32" (8mm)

0.20" (5mm)

4.25" (106.25mm)

3

662847013409

8203.20.60.60

EAR99

27111511

**USA** 











