




PKNI 10 B schwarz/black

Measuring and Testing Equipment:Sockets:4 mm system

| Description | Pole terminal with claw edge, captive insulated head and insulating ring. 6 mm |
|----------------------|--|
| Description | diameter nickel-plated brass threaded bolt with 2.6 mm diameter transverse hole. |
| | |
| | For insulated non-rotating installation in equipment chassis and switch panels up to |
| | 3.5 mm wall thickness. |
| Type | PKNI 10 B schwarz/black |
| Order No. | 930 136-100 |
| System | 4 mm system |
| Housing Color | black |
| Other standard types | red color, |
| | order no. 930 136-101 |



| Technical data | |
|--------------------------|-------------------|
| Type of contact | socket |
| Type of termination | M 6 thread |
| Rated voltage | DC 60 V |
| Rated current | 63 A |
| Contact resistance | 2 mOhm |
| Mounting | screw |
| Material | |
| Contact material | brass |
| Contact surface material | nickel-plated |
| Housing material | PF |
| Environmental conditions | |
| Temperature range | -25 °C to +100 °C |
| Inflammability class | |
| - | · |

Housing 94 V-0