

NX3225SA For OA / AV Mobile Communications/ Short-range Wireless


■ Features

Ideal for such as bluetooth, Wifi, smartphone and tablet pc.

- Compact and thin. (3.2 × 2.5 × 0.55 mm typ.)
- Excellent environmental characteristics, including heat and shock resistance.
- Lead-free. Meets the requirements for re-flow profiling using lead-free solder.

Pb Free

RoHS Compliant
Directive 2011/65/EU
Directive (EU) 2015/863



■ Specifications

Item	Model	NX3225SA	
		Standard	Optional
Standard		Standard	Optional
Nominal Frequency (MHz)		12 ≤ F ≤ 64	12 ≤ F ≤ 64
Overtone Order		Fundamental	Fundamental
Frequency Tolerance (25 ±3 °C)		±15 × 10 ⁻⁶	±10 × 10 ⁻⁶
Frequency versus Temperature Characteristics (with reference to +25 °C)		±25 × 10 ⁻⁶	±25 × 10 ⁻⁶ (Temp extended case, *1)
Operating Temperature Range (°C)		-40 to +85	-40 to +85 *1
Storage Temperature Range		-40 to +85	-40 to +85
Equivalent Series Resistance		Refer to *2	Refer to *1
Level of Drive (µW)		10 (Max. 200)	10 (Max. 200)
Load Capacitance (pF)		8	6 to 32
Frequency Aging (+25°C)		---	Max. ±3 × 10 ⁻⁶ / year *1
Specifications Number		STD-CQR-1	Refer to *3

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.

*1 If you have any other requests, NDK will study it.

*3 Ordering information: Overtone Order Fundamental / 3rd Overtone, the Operating Temperature Range, Frequency versus Temperature Characteristics, Frequency Tolerance, and Load Capacitance.

Ex. Model, Frequency (24.000000MHz 6digits), S1: Fundamental or S3 : 3rd overtone

– Operating Temperature Range (-40 to +85°C) – Frequency versus Temperature Characteristics (±25 × 10⁻⁶)


– Frequency Tolerance (±10 × 10⁻⁶) – Load Capacitance (8pF)

NX3225SA

24.000000MHz

S1-4085-25-10-8

■ Dimensions



Equivalent Series Resistance

Overtone Order	Nominal Frequency (MHz)	Equivalent Series Resistance Max. (Ω)
*2 Fundamental	12 ≤ F < 13	100
	13 ≤ F < 20	80
	20 ≤ F ≤ 64	50

If you have any other requests, NDK will study it.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NDK:

[NX3225SA-12MHZ-STD-CSR-6](#) [NX3225SA-16MHZ-STD-CSR-6](#) [NX3225SA-20.000M-STD-CRS-2](#) [NX3225SA-12.000M-STD-CRS-2](#) [NX3225SA-16.000M-STD-CRS-2](#) [NX3225SA-12MHZ-STD-CSR-3](#) [NX3225SA-20.000MHZ-STD-CSR-1](#) [NX3225SA-14.31818MHZ-STD-CSR-1](#) [NX3225SA-24.576MHZ-STD-CSR-1](#) [NX3225SA-27.000MHZ-STD-CSR-1](#) [NX3225SA-25.000M-STD-CSR-6](#) [NX3225SA-26.000M-STD-CSQ-1](#) [NX3225SA-25.000MHZ-STD-CSR-1](#) [NX3225SA-40.000MHZ-STD-CSR-1](#) [NX3225SA-25.000M-STD-CRS-2](#) [NX3225SA-12.000M-STD-CSR-3](#)