

Фото	Серия	Производитель	$P_{\text{вых}}$, Вт	$U_{\text{вх}}$, В перем. тока (В пост. тока)	$U_{\text{вых}}$, В	Число вых.	Темп. диап., °С	Размеры корпуса, мм
	DR-30	Mean Well	30	85...264 (120...370)	5, 12, 15, 24	1	-20...+50	78x93x56
	DR-45xx	Mean Well	45	85...264 (120...370)	5, 12, 15, 24	1	0...40	93x78x67
	LOK 4xxx	Power-One	50	85...264 (88...372)	5.1, 12, 24, 48, 12...15, 24...30, 48...60	1	-10...+50	38x90x116
	DRA60	Chinfa	60	90...265 (120...370)	5, 12, 24, 48	1	-10...+50	90x40,5x115
	DR60	Mean Well	60	85...264 (120...370)	5, 12, 15, 24	1	-20...+50	78x93x56
	DR-75	Mean Well	75	85...264 (120...370)	12, 24, 48	1	-10...60	56x126x100
	DR-120	Mean Well	120	88...132/176...264 (переключатель)	12, 24, 48	1	-10...60	66x126x100
	DRA120	Chinfa	120	93...132/186...264 (210...370)	12, 24, 48	1	-10...50	125x63,5x126 или 142x63, 5x126
	LWR 1xxx	Power-One	125	85...264 (90...350)	24.7, 37, 49.4, 25.7...29.3, 51.4...58.6	1	-10...50 или -40...60	103x114x103
	DRA240	Chinfa	240	93...132/186...264 (210...370)	24, 48	1	-10...50	125x83x126 или 142x83x126
	DRP-240	Mean Well	240	85...264 (120...370)	24, 48	1	-10...55	126x126x100