

1-888-CAPPLUGS

\$0.00

Sign In

View All Parts

[\(/catalog.html\)](/catalog.html)[Products \(/Catalog.html\)](/Catalog.html) > [Caps \(/catalog/caps.html\)](/catalog/caps.html) > VC SERIES

Caps

Round Vinyl Caps - VC SERIES

[View More Photos](#)

VC Series caps are extremely flexible and durable protective closures which are ideal for use as thread protectors, dust and moisture seals, pipe and stud end color coding, and for masking during painting or plating operations.

- Wide range of sizes
- Easy to use

- Vast color range available

Material: Vinyl

Standard Color: Black

Optional Color: White, Brown, Orange, Green, Gray, Blue, Red

Convert to Metric

*Selecting **Sample Only** Will default line item to standard sample status

How to Order

Caplug Sku#	Request Sample Only	Dim A (IN)	Dim B (IN)	Dim C (IN)	Size	Color	QTY	Cost
VC-054-10	<input type="checkbox"/>	0.054	0.09	0.625	Select ▼	Select ▼	<input type="text"/>	
VC-062-10	<input type="checkbox"/>	0.062	0.12	0.625	Select ▼	Select ▼	<input type="text"/>	
VC-072-10	<input type="checkbox"/>	0.072	0.13	0.625	Select ▼	Select ▼	<input type="text"/>	
VC-080-10	<input type="checkbox"/>	0.080	0.14	0.625	Select ▼	Select ▼	<input type="text"/>	
VC-093-12	<input type="checkbox"/>	0.093	0.15	0.750	Select ▼	Select ▼	<input type="text"/>	
VC-109-12	<input type="checkbox"/>	.109	.18	.750	Select ▼	Select ▼	<input type="text"/>	
VC-125-8	<input type="checkbox"/>	0.125	0.20	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-125-16	<input type="checkbox"/>	0.125	0.20	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-140-8	<input type="checkbox"/>	0.140	0.21	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-140-16	<input type="checkbox"/>	0.140	0.21	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-148-8	<input type="checkbox"/>	0.148	0.24	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-148-16	<input type="checkbox"/>	0.148	0.24	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-156-8	<input type="checkbox"/>	0.156	0.24	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-156-16	<input type="checkbox"/>	0.156	0.24	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-161-8	<input type="checkbox"/>	0.161	0.24	0.500	Select ▼	Select ▼	<input type="text"/>	

VC-161-16	<input type="checkbox"/>	0.161	0.24	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-172-8	<input type="checkbox"/>	0.172	0.25	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-172-16	<input type="checkbox"/>	0.172	0.25	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-180-8	<input type="checkbox"/>	0.180	0.26	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-180-16	<input type="checkbox"/>	0.180	0.26	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-187-8	<input type="checkbox"/>	0.187	0.27	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-187-16	<input type="checkbox"/>	0.187	0.27	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-187-24	<input type="checkbox"/>	0.187	0.27	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-203-8	<input type="checkbox"/>	0.203	0.29	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-203-16	<input type="checkbox"/>	0.203	0.29	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-218-8	<input type="checkbox"/>	0.218	0.31	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-218-16	<input type="checkbox"/>	0.218	0.31	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-224-8	<input type="checkbox"/>	0.224	0.31	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-224-16	<input type="checkbox"/>	0.224	0.31	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-234-8	<input type="checkbox"/>	0.234	0.32	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-234-16	<input type="checkbox"/>	0.234	0.32	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-240-8	<input type="checkbox"/>	0.240	0.33	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-240-16	<input type="checkbox"/>	0.240	0.33	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-250-8	<input type="checkbox"/>	0.250	0.35	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-250-16	<input type="checkbox"/>	0.250	0.35	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-270-10	<input type="checkbox"/>	0.270	0.37	0.625	Select ▼	Select ▼	<input type="text"/>	
VC-281-8	<input type="checkbox"/>	0.281	0.38	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-281-16	<input type="checkbox"/>	0.281	0.38	1.000	Select ▼	Select ▼	<input type="text"/>	

VC-290-8	<input type="checkbox"/>	0.290	0.40	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-290-16	<input type="checkbox"/>	0.290	0.40	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-304-8	<input type="checkbox"/>	0.304	0.41	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-304-16	<input type="checkbox"/>	0.304	0.41	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-312-8	<input type="checkbox"/>	0.312	0.42	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-312-16	<input type="checkbox"/>	0.312	0.42	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-312-24	<input type="checkbox"/>	0.312	0.43	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-343-8	<input type="checkbox"/>	0.343	0.45	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-343-16	<input type="checkbox"/>	0.343	0.45	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-375-8	<input type="checkbox"/>	0.375	0.50	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-375-16	<input type="checkbox"/>	0.375	0.50	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-406-8	<input type="checkbox"/>	0.406	0.53	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-406-16	<input type="checkbox"/>	0.406	0.53	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-437-8	<input type="checkbox"/>	0.437	0.56	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-437-16	<input type="checkbox"/>	0.437	0.56	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-460-8	<input type="checkbox"/>	0.460	0.58	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-460-16	<input type="checkbox"/>	0.460	0.58	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-467-8	<input type="checkbox"/>	0.467	0.58	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-467-16	<input type="checkbox"/>	0.467	0.58	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-485-16	<input type="checkbox"/>	0.485		1.000	Select ▼	Select ▼	<input type="text"/>	
VC-490-8	<input type="checkbox"/>	0.490	0.61	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-490-16	<input type="checkbox"/>	0.490	0.61	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-500-8	<input type="checkbox"/>	0.500	0.62	0.500	Select ▼	Select ▼	<input type="text"/>	

VC-500-16	<input type="checkbox"/>	0.500	0.62	1.000	Select ▼	Select ▼		
VC-531-8	<input type="checkbox"/>	0.531	0.65	0.500	Select ▼	Select ▼		
VC-531-16	<input type="checkbox"/>	0.531	0.65	1.000	Select ▼	Select ▼		
VC-562-8	<input type="checkbox"/>	0.562	0.69	0.500	Select ▼	Select ▼		
VC-562-16	<input type="checkbox"/>	0.562	0.69	1.000	Select ▼	Select ▼		
VC-600-8	<input type="checkbox"/>	0.600	0.73	0.500	Select ▼	Select ▼		
VC-600-16	<input type="checkbox"/>	0.600	0.73	1.000	Select ▼	Select ▼		
VC-610-8	<input type="checkbox"/>	0.610		0.500	Select ▼	Select ▼		
VC-610-16	<input type="checkbox"/>	0.610		1.000	Select ▼	Select ▼		
VC-625-8	<input type="checkbox"/>	0.625	0.76	0.500	Select ▼	Select ▼		
VC-625-16	<input type="checkbox"/>	0.625	0.76	1.000	Select ▼	Select ▼		
VC-625-24	<input type="checkbox"/>	0.625	0.77	1.500	Select ▼	Select ▼		
VC-640-8	<input type="checkbox"/>	0.640	0.77	0.500	Select ▼	Select ▼		
VC-640-16	<input type="checkbox"/>	0.640	0.77	1.000	Select ▼	Select ▼		
VC-665-8	<input type="checkbox"/>	0.665	0.80	0.500	Select ▼	Select ▼		
VC-665-16	<input type="checkbox"/>	0.665	0.80	1.000	Select ▼	Select ▼		
VC-687-8	<input type="checkbox"/>	0.687	0.81	0.500	Select ▼	Select ▼		
VC-687-16	<input type="checkbox"/>	0.687	0.81	1.000	Select ▼	Select ▼		
VC-690-8	<input type="checkbox"/>	0.690	0.82	0.500	Select ▼	Select ▼		
VC-690-16	<input type="checkbox"/>	0.690	0.82	1.000	Select ▼	Select ▼		
VC-725-8	<input type="checkbox"/>	0.725	0.86	0.500	Select ▼	Select ▼		
VC-725-16	<input type="checkbox"/>	0.725	0.86	1.00	Select ▼	Select ▼		

VC-750-8	<input type="checkbox"/>	0.750	0.88	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-750-16	<input type="checkbox"/>	0.750	0.88	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-812-8	<input type="checkbox"/>	0.812	0.94	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-812-16	<input type="checkbox"/>	0.812	0.94	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-812-24	<input type="checkbox"/>	0.812	0.95	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-825-8	<input type="checkbox"/>	0.825	0.96	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-825-16	<input type="checkbox"/>	0.825	0.96	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-843-8	<input type="checkbox"/>	0.843	0.98	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-843-16	<input type="checkbox"/>	0.843	0.98	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-870-8	<input type="checkbox"/>	0.870	1.01	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-870-16	<input type="checkbox"/>	0.870	1.01	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-875-8	<input type="checkbox"/>	0.875	1.02	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-875-16	<input type="checkbox"/>	0.875	1.02	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-875-24	<input type="checkbox"/>	0.875	1.02	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-937-8	<input type="checkbox"/>	0.937	1.08	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-937-16	<input type="checkbox"/>	0.937	1.08	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-985-8	<input type="checkbox"/>	0.985	1.13	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-985-16	<input type="checkbox"/>	0.985	1.13	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-1000-8	<input type="checkbox"/>	1.000	1.14	0.500	Select ▼	Select ▼	<input type="text"/>	
VC-1000-16	<input type="checkbox"/>	1.000	1.14	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-1000-24	<input type="checkbox"/>	1.000	1.14	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-1062-16	<input type="checkbox"/>	1.062	1.20	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-1090-16	<input type="checkbox"/>	1.090	1.22	1.000	Select ▼	Select ▼	<input type="text"/>	

VC-1125-16	<input type="checkbox"/>	1.125	1.27	1.000	Select ▼	Select ▼		
VC-1187-16	<input type="checkbox"/>	1.187	1.33	1.000	Select ▼	Select ▼		
VC-1250-16	<input type="checkbox"/>	1.250	1.39	1.000	Select ▼	Select ▼		
VC-1250-24	<input type="checkbox"/>	1.250	1.39	1.500	Select ▼	Select ▼		
VC-1312-16	<input type="checkbox"/>	1.312	1.45	1.000	Select ▼	Select ▼		
VC-1312-24	<input type="checkbox"/>	1.312	1.45	1.500	Select ▼	Select ▼		
VC-1375-16	<input type="checkbox"/>	1.375	1.52	1.000	Select ▼	Select ▼		
VC-1375-24	<input type="checkbox"/>	1.375	1.52	1.500	Select ▼	Select ▼		
VC-1437-16	<input type="checkbox"/>	1.437	1.58	1.000	Select ▼	Select ▼		
VC-1500-16	<input type="checkbox"/>	1.500	1.64	1.000	Select ▼	Select ▼		
VC-1500-24	<input type="checkbox"/>	1.500	1.64	1.500	Select ▼	Select ▼		
VC-1593-16	<input type="checkbox"/>	1.593	1.72	1.00	Select ▼	Select ▼		
VC-1625-16	<input type="checkbox"/>	1.625	1.77	1.000	Select ▼	Select ▼		
VC-1687-16	<input type="checkbox"/>	1.687	1.83	1.000	Select ▼	Select ▼		
VC-1750-16	<input type="checkbox"/>	1.750	1.89	1.000	Select ▼	Select ▼		
VC-1812-16	<input type="checkbox"/>	1.812	1.95	1.000	Select ▼	Select ▼		
VC-1875-16	<input type="checkbox"/>	1.875	2.02	1.000	Select ▼	Select ▼		
VC-1937-16	<input type="checkbox"/>	1.937	2.07	1.000	Select ▼	Select ▼		
VC-2000-16	<input type="checkbox"/>	2.000	2.14	1.000	Select ▼	Select ▼		
VC-2000-24	<input type="checkbox"/>	2.000	2.14	1.500	Select ▼	Select ▼		
VC-2125-16	<input type="checkbox"/>	2.125	2.27	1.000	Select ▼	Select ▼		
VC-2156-16	<input type="checkbox"/>	2.156	2.3	1.000	Select ▼	Select ▼		

VC-2250-16	<input type="checkbox"/>	2.250	2.40	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2250-24	<input type="checkbox"/>	2.250	2.40	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-2375-16	<input type="checkbox"/>	2.375	2.52	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2375-24	<input type="checkbox"/>	2.375	2.52	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-2460-16	<input type="checkbox"/>	2.460	2.61	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2500-16	<input type="checkbox"/>	2.500	2.65	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2500-24	<input type="checkbox"/>	2.500	2.65	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-2625-16	<input type="checkbox"/>	2.625	2.77	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2625-24	<input type="checkbox"/>	2.625	2.77	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-2687-16	<input type="checkbox"/>	2.687	2.84	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2750-16	<input type="checkbox"/>	2.750	2.91	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-2750-24	<input type="checkbox"/>	2.750	2.91	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-2875-16	<input type="checkbox"/>	2.875	3.03	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-3000-16	<input type="checkbox"/>	3.000	3.16	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-3000-24	<input type="checkbox"/>	3.000	3.16	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-3125-16	<input type="checkbox"/>	3.125	3.28	1.000	Select ▼	Select ▼	<input type="text"/>	
VC-3125-24	<input type="checkbox"/>	3.125	3.28	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-3250-18	<input type="checkbox"/>	3.255	3.41	1.125	Select ▼	Select ▼	<input type="text"/>	
VC-3375-18	<input type="checkbox"/>	3.375	3.53	1.125	Select ▼	Select ▼	<input type="text"/>	
VC-3500-18	<input type="checkbox"/>	3.500	3.66	1.125	Select ▼	Select ▼	<input type="text"/>	
VC-3500-24	<input type="checkbox"/>	3.500	3.66	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-3625-18	<input type="checkbox"/>	3.625	3.78	1.125	Select ▼	Select ▼	<input type="text"/>	
VC-3750-18	<input type="checkbox"/>	3.750	3.91	1.125	Select ▼	Select ▼	<input type="text"/>	

VC-3875-18	<input type="checkbox"/>	3.875	4.03	1.125	Select ▼	Select ▼		
VC-4000-20	<input type="checkbox"/>	4.000	4.16	1.250	Select ▼	Select ▼		
VC-4125-20	<input type="checkbox"/>	4.125	4.28	1.250	Select ▼	Select ▼		
VC-4187-20	<input type="checkbox"/>	4.187	4.34	1.250	Select ▼	Select ▼		
VC-4250-20	<input type="checkbox"/>	4.250	4.41	1.250	Select ▼	Select ▼		
VC-4375-20	<input type="checkbox"/>	4.375	4.53	1.250	Select ▼	Select ▼		
VC-4500-20	<input type="checkbox"/>	4.500	4.66	1.250	Select ▼	Select ▼		
VC-4750-20	<input type="checkbox"/>	4.750	4.91	1.250	Select ▼	Select ▼		
VC-4813-32	<input type="checkbox"/>	4.813	5.00	2.00	Select ▼	Select ▼		
VC-4875-32	<input type="checkbox"/>	4.875	5.05	2.00	Select ▼	Select ▼		
VC-5000-22	<input type="checkbox"/>	5.000	5.18	1.375	Select ▼	Select ▼		
VC-5187-22	<input type="checkbox"/>	5.187	5.36	1.375	Select ▼	Select ▼		
VC-5375-22	<input type="checkbox"/>	5.375	5.55	1.375	Select ▼	Select ▼		
VC-5500-22	<input type="checkbox"/>	5.500	5.68	1.375	Select ▼	Select ▼		
VC-5625-32	<input type="checkbox"/>	5.625	5.80	2.00	Select ▼	Select ▼		
VC-5750-22	<input type="checkbox"/>	5.750	5.93	1.375	Select ▼	Select ▼		
VC-6000-24	<input type="checkbox"/>	6.000	6.18	1.500	Select ▼	Select ▼		
VC-6125-32	<input type="checkbox"/>	6.125	6.30	2.00	Select ▼	Select ▼		
VC-6250-24	<input type="checkbox"/>	6.250	6.43	1.500	Select ▼	Select ▼		
VC-6500-24	<input type="checkbox"/>	6.500	6.68	1.500	Select ▼	Select ▼		
VC-6750-24	<input type="checkbox"/>	6.750	6.93	1.500	Select ▼	Select ▼		
VC-6875-32	<input type="checkbox"/>	6.875	7.05	2.00	Select ▼	Select ▼		

VC-7000-24	<input type="checkbox"/>	7.000	7.18	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-7250-24	<input type="checkbox"/>	7.250	7.43	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-7375-32	<input type="checkbox"/>	7.375	7.55	2.00	Select ▼	Select ▼	<input type="text"/>	
VC-7500-24	<input type="checkbox"/>	7.500	7.68	1.500	Select ▼	Select ▼	<input type="text"/>	
VC-7750-28	<input type="checkbox"/>	7.750	7.93	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-8000-28	<input type="checkbox"/>	8.000	8.18	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-8500-28	<input type="checkbox"/>	8.500	8.68	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-8750-28	<input type="checkbox"/>	8.750	8.93	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-9000-28	<input type="checkbox"/>	9.000	9.20	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-9250-28	<input type="checkbox"/>	9.250	9.45	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-9375-28	<input type="checkbox"/>	9.375	9.57	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-9875-28	<input type="checkbox"/>	9.877	10.07	1.750	Select ▼	Select ▼	<input type="text"/>	
VC-10000-32	<input type="checkbox"/>	10.000	10.20	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-10312-32	<input type="checkbox"/>	10.312	10.51	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-10750-32	<input type="checkbox"/>	10.750	10.95	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-11000-32	<input type="checkbox"/>	11.000	11.20	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-11375-32	<input type="checkbox"/>	11.375	11.57	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-11750-32	<input type="checkbox"/>	11.750	11.95	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-12000-32	<input type="checkbox"/>	12.000	12.20	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-12250-32	<input type="checkbox"/>	12.250	12.45	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-12500-32	<input type="checkbox"/>	12.500	12.70	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-12625-32	<input type="checkbox"/>	12.625	12.82	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-12875-32	<input type="checkbox"/>	12.875	13.07	2.000	Select ▼	Select ▼	<input type="text"/>	

VC-13250-32	<input type="checkbox"/>	13.250	13.47	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-13500-32	<input type="checkbox"/>	13.500	13.72	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-13600-32	<input type="checkbox"/>	13.600	13.82	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-14000-32	<input type="checkbox"/>	14.000	14.22	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-14250-32	<input type="checkbox"/>	14.250	14.47	2.00	Select ▼	Select ▼	<input type="text"/>	
VC-14500-32	<input type="checkbox"/>	14.500	14.72	2.00	Select ▼	Select ▼	<input type="text"/>	
VC-15000-32	<input type="checkbox"/>	15.000	15.22	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-15625-32	<input type="checkbox"/>	15.620	15.84	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-15875-32	<input type="checkbox"/>	15.875	16.11	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-16000-32	<input type="checkbox"/>	16.000	16.24	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-16500-32	<input type="checkbox"/>	16.500	16.74	2.000	Select ▼	Select ▼	<input type="text"/>	
VC-17375-40	<input type="checkbox"/>	17.375	17.61	2.500	Select ▼	Select ▼	<input type="text"/>	
VC-18000-40	<input type="checkbox"/>	18.000	18.24	2.500	Select ▼	Select ▼	<input type="text"/>	
VC-19000-40	<input type="checkbox"/>	19.000	19.24	2.500	Select ▼	Select ▼	<input type="text"/>	
VC-20000-40	<input type="checkbox"/>	20.000	20.24	2.500	Select ▼	Select ▼	<input type="text"/>	



[Shopping Cart \(/cart.html\)](/cart.html) [Contact Us \(/content/contact.html\)](/content/contact.html) [About Us \(/content/about.html\)](/content/about.html) [Returns \(/content/returns.html\)](/content/returns.html) [Privacy \(/content/privacy.html\)](/content/privacy.html) [Terms & Conditions \(/content/terms.html\)](/content/terms.html)

Quick Links: [About Us \(/content/about.html\)](/content/about.html) [News & Events \(/news.html\)](/news.html) [Military & NAS Specifications \(/content/military-nas-specifications.html\)](/content/military-nas-specifications.html) [Cross Reference Guide \(/content/cross-reference-guide.html\)](/content/cross-reference-guide.html)

Product [Caps \(/catalog/caps.html\)](/catalog/caps.html) [Plugs \(/catalog/plugs.html\)](/catalog/plugs.html) [Shercon Masking \(/catalog/shercon_masking.html\)](/catalog/shercon_masking.html) [Packaging Products and Plastic Netting \(/catalog/packaging_products_and_plastic_netting.html\)](/catalog/packaging_products_and_plastic_netting.html) [More Product Protection \(/catalog/more_product_protection.html\)](/catalog/more_product_protection.html) [Thread Protectors from Tri-Star \(/catalog/tristar-thread-protection.html\)](/catalog/tristar-thread-protection.html) [Evergreen Labware \(/catalog/evergreen-labware.html\)](/catalog/evergreen-labware.html) [View all \(/catalog.html\)](/catalog.html)
Materials [Polyethylene \(/catalog/polyethylene.html\)](/catalog/polyethylene.html) [Vinyl \(/catalog/vinyl.html\)](/catalog/vinyl.html) [Silicone \(/catalog/silicone.html\)](/catalog/silicone.html) [Molded Rubber \(/catalog/oem_rubber.html\)](/catalog/oem_rubber.html) [Adhesives \(/catalog/adhesives.html\)](/catalog/adhesives.html) [PETG \(/catalog/petg.html\)](/catalog/petg.html) [Additional Materials](#)

[\(/catalog/additional_materials.html\)](/catalog/additional_materials.html)

Applications [Masking \(/catalog/masking.html\)](/catalog/masking.html) [Medical \(/catalog/medical.html\)](/catalog/medical.html) [Thread & Flange Protection \(/catalog/thread_protection.html\)](/catalog/thread_protection.html)

[Automotive \(/catalog/automotive.html\)](/catalog/automotive.html) [Electronics \(/catalog/electronics.html\)](/catalog/electronics.html) [Hydraulics \(/catalog/hydraulics.html\)](/catalog/hydraulics.html) [Compressed Gas](/catalog/compressed_gas.html)

[\(/catalog/compressed_gas.html\)](/catalog/compressed_gas.html) [Aviation \(/catalog/aviation.html\)](/catalog/aviation.html) [Packaging & Netting \(/catalog/packaging_and_netting.html\)](/catalog/packaging_and_netting.html)

Custom Parts [Design a Part \(/catalog/design_part.html\)](/catalog/design_part.html) [Molding Capabilities \(/catalog/molding_capabilities.html\)](/catalog/molding_capabilities.html)

Service & Support [Find a Sales Representative \(/salesrepfinder.html\)](/salesrepfinder.html) [Learning Center \(/catalog/learning_center.html\)](/catalog/learning_center.html) [Download Catalog](/catalog/download_catalog.html)

[\(/catalog/download_catalog.html\)](/catalog/download_catalog.html) [Request a Quote \(/request-quote.html\)](/request-quote.html) [How to Order \(/catalog/ordering.html\)](/catalog/ordering.html) [FREE Samples Available](/catalog/request_free_samples.html)

[\(/catalog/request_free_samples.html\)](/catalog/request_free_samples.html) [Contact Us \(/catalog/contact.html\)](/catalog/contact.html) [Quality Assurance & Memberships \(/catalog/Quality.html\)](/catalog/Quality.html)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Caplugs:](#)

[VC-1250-16](#)