





Rev	AWO #	Description	Date	Appr
-		RELEASED	11/08/04	

APPROVED: _____
 DATE: _____ TITLE: _____



**RECOMMENDED
PCB LAYOUT**



A = .100 [2.54] X No. of Positions Per Row
 Positions available: 6, 8, 14, 16, 18, 20, 24 & 26

SPECIFICATIONS:

- Material: Insulator: PBT, glass reinforced, rated UL 94V-0
- Insulator Color: Black
- Contacts: Phosphor Bronze
- Plating: Tin over Copper underplate overall
- Electrical: Operating voltage: 250 VAC max
- Current rating: 1 Amp max
- Contact resistance: 20 mohms max
- Insulation resistance: 5000 Mohms min @ 500 VDC
- Dielectric withstanding voltage: 1000 VAC for 1 minute
- Temperature Rating: Operating temperature: -55°C to +105°C
- Packaging: Anti-ESD plastic tubes

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: IC SOCKET, .300 ROW CENTERS, PCB,
 TIN PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLDS
.X ± .10	ØX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXXX ± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

SIZE	PART NO.	SCALE	SHEET 1 OF 1
X	ICS-3XX-T	NTS	