

Automotive Switch


Q-1038

TYPE: **IRS-101E-8C**


SPECIFICATIONS

Contact Type: SPST
Rating: 16A 12V DC
Contact R: 50mΩ max
Insulation R: 500V DC 100MΩ min
Dielectric Strength: 1 Minute 1500V AC
Operating Temperature: -25°C ~ +85°C
Electrical Life: 10, 000 Cycles

Outline Drawing



Mounting



Circuitry

