

# Automotive Rocker Switch

**Q-10461**

TYPE: **R13-238B8**

**Rocker**





**Waterproof**



## SPECIFICATIONS

Rating: 16A 12V DC  
Contact R: 50mΩ max  
Insulation R: 500V DC 100MΩ min  
Dielectric Strength: 1 Minute 1500V AC  
Operating Temperature: -25°C ~ +85°C  
Electrical Life: 10,000 Cycles


Outline Drawing



Mounting



Circuitry



3P SPST (ILLUMINATED)