

## Medium Toggle Switch


**Q-348**

TYPE: **KN3(B)-403A**


### SPECIFICATIONS

Rating: 10A 125V AC; 6A 250V AC  
 Contact R: 50mΩ max  
 Insulation R: 500V DC 100MΩ min  
 Dielectric Strength: 1 Minute 1500V AC  
 Operating Temperature: -25°C ~ +85°C  
 Electrical Life: 10, 000 Cycles

Outline Drawing



Mounting



Circuitry

