


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1720630311](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit Female Crimp Terminal, 14 and 16 AWG 15µ" Gold (Au) Plating, Reel

Documents:

Drawing (PDF)	Test Summary TS-76823-001-001 (PDF)
Product Specification PS-76823-100-001 (PDF)	Test Summary TS-76823-100-001 (PDF)
Application Specification AS-76823-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-76823-001 (PDF)	Product Literature (PDF)



Series image - Reference only

General

Product Family	Crimp Terminals
Series	172063
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Mega-Fit Power Connectors
Product Literature Order No	987650-5401
Product Name	Mega-Fit
UPC	887191474571

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	0.322/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.75mm (0.148")
Wire Size AWG	14, 16
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	23.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-76823-100-001
Packaging Specification	PK-76823-001
Product Specification	PS-76823-100-001
Sales Drawing	SD-76823-0100-001
Test Summary	TS-76823-001-001, TS-76823-100-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172063](#) Series

Use With

Mega-Fit Receptacle Housing [171692](#) ,
[170001](#)