


Shellsize	A	B	C	Ø D	E	F	* G ± 1	Cable Ø	Part-No.
2	48	33,3	22 A/F	25	36	21	54,6	9 - 11	15-004670
3	62	47,04	24 A/F	27	44	21	67,7	10 - 12	15-004680
4	78	63,5	28 A/F	31	53	25,2	77,2	14 - 16	15-004690
5	75,6	61,1	28 A/F	31	53	23,8	77,2	14 - 16	15-004700

(1:1)



\* COMPLETELY TIGHTENED

**NOTES:**

- MATERIALS:**  
HOOD: PBT GF UL94 V-0 BLACK  
FRONTSEALING: SILICONE VMQ BLUE  
SCREW: STAINLESS STEEL  
O-RING: NBR BLACK
- TEMPERATURE RANGE:** -30°C TO +90°C
- RECOMMENDED TORQUE FOR SCREW:**  
35Ncm (3.1 in.LB)  
MAX. TORQUE: 68Ncm (6 in.LB)
- SINGLE PACKED**

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	tolerance ± 0,3 unless otherw. specified		dim. in mm		scale: 1,5:1 (1:1)
	date		name		material: SEE NOTES
	drawn	19.09.12	Huether		title: WATER RESISTANT D-SUB HOOD 15-50 POS. JACKSCREW 4-40UNC STAINLESS STEEL
	appd.	11.10.12	Kuehle		
	norm				
	d-old				dwg no:
a	Origin			15K1A1152	DIN-A3
rev.	description			date	name

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[15-004700](#) [15-004680](#) [15-004690](#)