

## FEATURES

- The body is available in burnished steel with black oxide finish or stainless steel
- Hardened plunger
- Knob material – high impact resistant thermoplastic
- Knob finish – matt
- Standard colour – black knob
- Comes at standard with 90° locking rest position in plunger body

## RS PRO M10 Index Plunger, 51mm Long

RS Stock No.: 237-390



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description ATTRIBUTE 1

These spring-loaded hand retractable plungers from our own RS PRO brand are designed to prevent any change in locking position due to lateral force. Pulling up on the handle retracts the plunger pin into the body.

## General Specifications


<b>Type</b>	Index Plunger
<b>Body Material</b>	Burnished steel or stainless steel
<b>Thread Size</b>	M10x1.0
<b>Applications</b>	Ideal for applications where precision positioning is needed, such as rotary indexing heads. Clamping of adjustable elements; Positioning of work pieces; Latching of mechanisms
<b>Rest Position</b>	Yes
<b>Surface Treatment</b>	Black oxide finish or stainless steel

## Mechanical Specifications

<b>Length</b>	51mm
---------------	------

## Approvals

<b>Compliance/Certifications</b>	RoHS
----------------------------------	------



Part No.	A	B	C	D	E	Thread size	Plunger diameter (mm)	Body material
237766	21	51	5	17	5	M10x1.0	5	Burnished steel
237788	25	61	6	20	6	M12x1.5	6	Burnished steel
237794	31	76	8	26	7	M16x1.5	8	Burnished steel
237390	21	51	5	17	5	M10x1.0	5	Stainless steel
237401	25	61	6	20	6	M12x1.5	6	Stainless steel
237407	31	76	8	26	7	M16x1.5	8	Stainless steel

