

## Specification Sheet

Part Number: 151-01567

Two-piece ratcheting wedge design allows for easy, positive-locking size adjustment.

Peel and stick 3M™ VHB™ adhesive inside clip increases grip and enables one-hand installation.

Heat-stabilized, glass-filled PA66 assembly delivers remarkable extraction force without drilling.

Three sizes cover a wide range of mounting thicknesses, reducing part inventory.

4-way, wide slot accommodates our heavy-duty and Wide-Strap Series Cable Ties.



<b>Article Number</b>	151-01567
<b>Type</b>	BCCLGA
<b>Color</b>	Gray (GY) Black (BK)
<b>Quantity Per</b>	bag

<b>Product Description</b>	The Wedge Clip, paired with any HellermannTyton heavy duty Cable Tie, routes cables along a frame or rail in vertical or horizontal applications. A robust design and durable materials make it ideal for extreme-duty applications. The integrated wedge mechanism slides along a stepped grade until snug against the mounting surface. Inside the clip is a 3M™ VHB™ (Very High Bond) adhesive pad, which actually builds strength over time. This holds the clip to the work surface instantly, enabling installers to place it into position without worrying about it falling off prior to fastening. The combination of adhesive and the clip's vice-like compression result in incredible extraction force without the need to drill holes. The Wedge Clip is offered in three sizes.
<b>Short Description</b>	Wedge Clip, 0.31"–0.51" Panel Thickness, PA66HSGF30, Black/Gray, 200/bag
<b>Global Part Name</b>	BCCLGA-PA66HSGF30-BK/GY
<b>Length L (Imperial)</b>	1.21
<b>Length L (Metric)</b>	30.8
<b>Width W (Imperial)</b>	1.13
<b>Width W (Metric)</b>	28.6
<b>Height H (Imperial)</b>	1.70
<b>Height H (Metric)</b>	43.10
<b>Panel Thickness Min (Imperial)</b>	0.315
<b>Panel Thickness Max (Imperial)</b>	0.512
<b>Panel Thickness Min (Metric)</b>	8.0

<b>Panel Thickness Max (Metric)</b>	13.0
<b>Material</b>	Polyamide 6.6, heat stabilized, glass fiber reinforced (PA66HSGF30%)
<b>Material Shortcut</b>	PA66HSGF30
<b>Adhesive</b>	Acrylic foam
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature</b>	-40°F to +284°F (-40°C to +140°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	200
<b>Package Quantity (Metric)</b>	200
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01567](#)