

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1726770100](#)
Status: **Active**
Overview:
Description: SolderRight Right-Angle Direct Solder Terminal 22-24 AWG In-Line Mount, Tin

Agency Certification

UL E470987

General

Product Family Crimp Terminals
 Series [172677](#)
 Application Power, Wire-to-Board
 Crimp Quality Equipment Yes
 Overview solderright
 Product Name SolderRight
 Taxonomy Crimp Terminals
 UPC 887191934020

Physical

Gender N/A
 Material - Metal Brass
 Material - Plating Mating Matte Tin
 Material - Plating Termination Matte Tin
 Net Weight 0.044/g
 Packaging Type Reel
 Plating min - Mating 1.524µm
 Plating min - Termination 1.524µm
 Termination Interface: Style Through Hole
 Wire Insulation Diameter 1.40-1.60mm
 Wire Size AWG 22, 24
 Wire Size mm² 0.20-0.33

Electrical

Current - Maximum per Contact 7.5A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-172249-001-001
 Product Specification PS-172249-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained per -
 D(2022)9120-DC (17
 Jan 2023)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172677](#) Series

Mates With

Solder straight to PCB

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Insertion Tool [638121600](#)

for SolderRight
 Terminals

Hand Crimp Tool for [638273200](#)

SolderRight In-Board

Terminals

FineAdjust Applicator [639029900](#)

for SolderRight In-

Board Terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION