

Specification Sheet

Part Number: ET660



PVC Tape is ideal for general purpose electrical applications. Economical way to splice, terminate and insulate wire and cables.

Meets Mil-Std. MIL-1-7798-A.

Electrical Tape, .75" x 66' Roll, 7.0 mil Thick, PVC, Black, 10 rolls/pkg

Article Number 904-00008

Type ET66

Color Black (BK)

Quantity Per reel

Product Description PVC electrical tape provides fast and easy color coding, cable splicing, terminating, and wire insulating. These conformable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.

Short Description Electrical Tape, .75" x 66' Roll, 7.0 mil Thick, PVC, Black, 10 rolls/pkg

Global Part Name	ET66-PVC-BK
Minimum Tensile Strength (Imperial)	15.4
Length L (Imperial)	66.0
Length L (Metric)	20.12
Width W (Imperial)	0.75
Width W (Metric)	19.05
Thickness T (Imperial)	7.0
Material	Flexible Polyvinyl Chloride (PVC)
Material Shortcut	PVC
US MIL SPEC	MIL-1-7798-A
Operating Temperature	+20°F to 176°F (-7°C to +80°C)
UL Listed (US)	Yes
Package Quantity (Imperial)	10

Package Quantity (Metric) 10

Customs Number 3919102020

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)