

CONSTANT VOLTAGE LED DRIVER

12VDC 100WATT



POWERPAX: LED-DR-12V-100W-SLIM

Features:

- Input Voltage 200-240vac
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 1 Year Warranty



Description:

The Range of 100 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-12V-100W-SLIM
Output Voltage Rating	12Vdc \pm 5%
Output Current Range	8.33A Max
Rated Power	100 Watt
Dimensions	320.6(L) x 26.8(W) x 18.2(H) mm
Input Voltage Range	200-240VAC
Input Voltage Frequency	50-60Hz
Input power	<118W
Efficiency	\geq 90%
Power Consumption Without Load	<0.5W
Overload Protection	Ta, input 0.94-1.06 times rated voltage, output 2 times of rated load
Short Circuit Protection	Ta, input 0.94-1.06 times rated voltage, output short circuit for 1 hour
Automatically Restart	Yes
Working Temperature	-20°C to +45°C
Relative Humidity	45% to 85%
MTBF	30000hr
EMC emission	EN55015
EMC Immunity	EN61547
Safety Standards	IEC61347-1, IEC61347-2-13(with lights IEC60598)

POWERPAX

General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

CONSTANT VOLTAGE LED DRIVER 12VDC 100WATT

POWERPAX: LED-DR-12V-100W-SLIM

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

POWERPAX