

DS1011 SERIES

SHROUDED HEADER PITCH 2.54mm




ZHENQIN

MATERIAL


- ◆ Insulator: Thermoplastic (UL 94V-0)
- ◆ Color: See ordering information
- ◆ Contact: Copper Alloy
- ◆ Contact Plated: See ordering information

1000



SPECIFICATION

- ◆ Storage Temperature: -20-70°C
- ◆ Operating Temperature: 0-85°C
- ◆ Contact Resistance: 20mΩ max. (initial)
- ◆ Insulation Resistance: 1,000MΩ min.
- ◆ Dielectric Withstanding Voltage: AC 1,000V per minute



Ordering Information

UNIT:mm

Series No.	No. of Contacts	Mounting Type	Ejector Type	Contact Plating	Housing Color
DS1011	34	S	L	SI	B
	10 26 50	S: Straight	L: Long	SI: Full Gold	B: Black
	14 30 60	R: R/A	S: Short	TI: Selective Gold	G: Gray
	16 34 64		N: W/O		
	20 40				

DS1011-01



SHROUDED HEADER PITCH 2.00mm

MATERIAL

- ◆ Insulator: Thermoplastic (UL 94V-0)
- ◆ Color: See ordering information
- ◆ Contact: Copper Alloy
- ◆ Contact Plated: See ordering information

SPECIFICATION

- ◆ Storage Temperature: -20-70°C
- ◆ Operating Temperature: 0-85°C
- ◆ Contact Resistance: 20mΩ max. (initial)
- ◆ Insulation Resistance: 1,000MΩ min.
- ◆ Dielectric Withstanding Voltage: AC 1,000V per minute



Ordering Information

UNIT:mm

Series No.	No. of contacts	Mounting Type	Ejector Type	Contact Plating	Housing Color
DS1011-01	34	S	L	SI	B
	10 26 34	R/A	L: Long	SI: Selective Gold	B: Black
	40 44 50	SMT	S: Short	G: All Gold Plated	G: Gray
	60	S/T	N: W/O		